

1.32/1

Set of internal and external extractors

11-pieces

Code	ETIM
8015260	EC011834
EAN	UNSPSC
4036976105476	27-11-17-12
Country of origin	eCl@ss
Germany	21-04-15-01
Customs tariff number	
82055980	



Article description

- Sets with internal extractors, counter supports, puller chucks, external extractors and stud extractors
- In robust sheet metal case

Article parts list

1.30/2 Internal extractor 12-15 mm ,1.30/3 Internal extractor 15-19 mm ,1.30/4 Internal extractors 19-25 mm ,1.30/4A Internal extractors 25-30 mm ,1.30/5 Internal extractor 30-35 mm ,1.30/6 Internal extractor 35-45 mm ,1.36/1 Counter support for 1.30/0 - 1.30/5 ,1.36/2 Counter support for 1.30/6 - 1.30/7 ,1.19/OXS Puller 3-arm XS hook 50x70 mm ,1.12/02 Pole terminal puller 2-arm 60x40 mm ,1.06/1 Universal puller 2-arm 90x100 mm ,132/199B Sheet metal box empty

Article information

Contents (Qty of pieces)	11	Spindle anti-slip device	no
Graduation	no	Screws included	no
reversible arms available	no	Anti-slip device on the spindle	no
Clamping bracket available	no	Exchangeable spindle tip	no
Net weight [kg]	10,4 kg	Can be retrofitted with hydraulic spindle	no
Hook brake available	no	Total length [mm]	425 mm
Hook can be moved parallel	no	Total width [mm]	330 mm
Quick release lever available	no	Total height [mm]	75 mm
3D data available	no		