

Datasheet

Steel Girder Suspension Clip & Hanger, 1.5 → 3 mm

RS Stock number [277480](#)



Description

- Chain/Wire Hangers
- Either horizontal flange or vertical flange

Specification

- | | |
|----------------------------|------------|
| • Flange Orientation | Horizontal |
| • Flange Thickness | 1.5 → 3 mm |
| • Flange Thickness Maximum | 3mm |
| • Flange Thickness Minimum | 1.5mm |
| • Material | Steel |
| • Maximum Load | 72kg |

Measurements

- | | |
|---------------|-----------|
| • T | 1.5 – 3mm |
| • Ø | 6.5mm |
| • A | 16mm |
| • B | 12.5mm |
| • Load Rating | 72kg |

