

FEATURES

- Metal flexible conduit with PVC tube cover
- High tensile strength and waterproof
- Good resistance in bending
- High heat and erosion

RS PRO PVC Coated Galvanised Steel Flexible Conduit Black 20mm x 10m

RS Stock No.: 784-0108



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

--

General Specifications

Conduit Type	Flexible, Split
Material	Galvanised Steel
Colour	Black
Coating Material	PVC

Mechanical Specifications

Nominal Diameter	20mm
Outer Diameter	20mm
Interior Diameter	16mm
Length	10mm

Approvals

Compliance/Certifications	2011/65/EU and 2015/863
Standards Met	ANSI/ESD S20.20:2014 and BS EN 61340-5-1:2007



Dimensions – mm

RS Item No.	Description	I.D.		O.D. (mm)	Packing
		Inch	mm		
784-0094	PVC covered metal conduit 12mm 25m	1/3	8.2	11	25m / roll
784-0098	PVC covered metal conduit 16mm 25m	1/2	12.6	16.2	25m / roll
784-0108	PVC covered metal conduit 20mm 10m	5/8	16	20	10m / roll
784-0101	PVC covered metal conduit 20mm 25m	5/8	16	20	25m / roll
784-0105	PVC covered metal conduit 25mm 10m	3/4	21	24.4	10m / roll