

FEATURES

- To DIN6926 Grade 8 steel, bright zinc plated
- Self-locking due to nylon insert
- Plain faced flange

RS PRO, M6, Bright Zinc Plated Steel Nylon Insert Lock Nut

RS Stock No.: 275-614



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted RS PRO brand, these lock nuts contain a nylon insert for safe and secure fastening. They are designed to remain secure despite conditions of severe vibration. They have a large flat integrated washer which allows for load distribution against a surface, and have a hexagonal structure for ease of screwing and unscrewing with a spanner or appropriate socket. The nut is made from grade 8 carbon alloy steel with bright zinc plating, for durability and environmental resistance over a long period of use.

There are various metric sizes available:

275-608 is an M5 self-locking nut 275-614 is an M6 self-locking nut

275-620 is an M8 self-locking nut

275-636 is an M10 self-locking nut

275-642 is an M12 self-locking nut

General Specifications

Thread Size	M6
Type	Nylon Insert
Material	Stainless Steel
Finish	Bright Zinc Plated
Grade	8
Driving Features	Hexagon
Nut Form	Flanged
Applications	Domestic appliances such as washers and dryers, Industrial machinery, Automotive industry

Mechanical Specifications

Specification	DIN 6926
Thickness	8.74mm to 9.1mm
Thread Pitch	1
Width Across Flats	9.78mm to 10mm
Wrenching Height	5.7mm

Approvals

Compliance/Certifications

RoHS

