



### Main

Range	Odace
Product or component type	Cover plate
Product destination	Socket-outlet
Type of packing	Plastic bag
Quantity per set	Set of 10

### Complementary

Outlet poles configuration	2P + E
Outlet standard deviation	French
Fixing mode	Clip-in
Colour tint	Aluminium
Material	Thermoplastic ABS-UV stabilised
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

### Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
IK degree of protection	IK04

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations