1362 - 1363 - 1364 - 1370 : Set of Dies



The + product :


Precision machined from a special alloy steel guaranteeing a high cutting performance, excellent resilience and hardness.
Cutting profile with a clearance angle to reduce friction.

Description

Compatible with manual interchangeable head threader, Mini Phenix and Phenix III, according to capacity.

For tubes complying with the EN 10255 S and EN 10255 W standards (former NFA 49115 and NFA 49145 standard medium and heavy duty series); only light series tubes are not recommended.

TIP: *Virax cutting oil must be used for lubrication in all threading operations.*



Type : choice of dies according to their compatibility with the old generation heads (1362 - 1364 - 1370) or new generation (1363). The new generation heads are identifiable thanks to the marking 1363xx on their cap.

References

Sku	Type	Type of thread	For	Ø "	Ø mm	kg
136201	Steel - 1362	Right hand BSPT	136231	1/8	6/10	0,060
136202	Steel - 1362	Right hand BSPT	136232	1/4	8/13	0,055
136320	Steel - 1363	Right hand BSPT	136340	1/4	8/13	0,058
136203	Steel - 1362	Right hand BSPT	136233	3/8	12/17	0,055
136321	Steel - 1363	Right hand BSPT	136341	3/8	12/17	0,055
136322	Steel - 1363	Right hand BSPT	136342	1/2	15/21	0,060
136205	Steel - 1362	Right hand BSPT	136235	3/4	20/27	0,070
136323	Steel - 1363	Right hand BSPT	136343	3/4	20/27	0,065

Sku	Type	Type of thread	For	Ø "	Ø mm	kg
136206	Steel - 1362	Right hand BSPT	136236	1	26/34	0,115
136324	Steel - 1363	Right hand BSPT	136344	1	26/34	0,115
136207	Steel - 1362	Right hand BSPT	136237	1.1/4	33/42	0,115
136325	Steel - 1363	Right hand BSPT	136345	1.1/4	33/42	0,115
136408	Steel - 1364	Right hand BSPT	136438 - 136439	1.1/2 - 2	40/49 - 50/60	0,150
136326	Steel - 1362	Right hand BSPT	136346 - 136347	1.1/2 - 2	40/49 - 50/60	0,150
136327	Steel - 1363	Right hand BSPT	136348	1.1/2	40/49	0,155
136328	Steel - 1363	Right hand BSPT	136349	2	50/60	0,155
136213	Steel - 1362	Left hand BSPT	136243	3/8	12/17	0,055
136216	Steel - 1362	Left hand BSPT	136246	1	26/34	0,115
136418	Steel - 1364	Left hand BSPT	136448 - 136449	1.1/2 - 2	40/49 - 50/60	0,150
136222	Steel - 1362	NPT	136252	1/4	8/13	0,060
136330	Steel - 1363	NPT	136350	1/4	8/13	0,060
136223	Steel - 1362	NPT	136253	3/8	12/17	0,055
136331	Steel - 1363	NPT	136351	3/8	12/17	0,052
136224	Steel - 1362	NPT	136254	1/2	15/21	0,060
136332	Steel - 1363	NPT	136352	1/2	15/21	0,060
136225	Steel - 1362	NPT	136255	3/4	20/27	0,070
136333	Steel - 1363	NPT	136353	3/4	20/27	0,070
136226	Steel - 1362	NPT	136256	1	26/34	0,115
136334	Steel - 1363	NPT	136354	1	26/34	0,114
136335	Steel - 1363	NPT	136355	1.1/4	33/42	0,115
136428	Steel - 1364	NPT	136458 - 136459	1.1/2 - 2	40/49 - 50/60	0,150
136336	Steel - 1363	NPT	136356 - 136357	1.1/2 - 2	40/49 - 50/60	0,149
136337	Steel - 1363	NPT	136358	1.1/2	40/49	0,155
136338	Steel - 1363	NPT	136359	2	50/60	0,155
137003	Stainless steel - 1370	Right hand BSPT	137043	3/8	12/17	0,055
137004	Stainless steel - 1370	Right hand BSPT	137044	1/2	15/21	0,065
137005	Stainless steel - 1370	Right hand BSPT	137045	3/4	20/27	0,072
137007	Stainless steel - 1370	Right hand BSPT	137047	1.1/4	33/42	0,120

