

---

Item no.: 2004-1207  
Product description: 2-Conductor earth terminal block suitable for Ex e applications

---



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Product group	22 (TOPJOB S RAIL-MOUNTED TERMINAL BLOCKS)
Cross section [mm <sup>2</sup> ]	0.5 - 4 mm <sup>2</sup>
Cross section [AWG]	20 - 10 AWG
Connection method	CAGE CLAMP®S Connection
Cross section [mm <sup>2</sup> ]	0.5 - 6 mm <sup>2</sup>
Cross section [AWG]	20 - 10 AWG
Wiring method	s + f-st
Connection method	CAGE CLAMP®S Connection
Nominal current (Ex e II)	30 A
Weight	12.194 g
Color	green-yellow
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	1
Height	33 mm
Height	1.299 in
Width	6.2 mm
Width	0.244 in
Depth	52.5 mm

Depth	2.07 in
Strip length from	11 mm
Strip length to	13 mm



Strip length	0.47 in
Customs Tariff No.	85369010
Country of Origin	Deutschland
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
2004-1207	ABS	05-HG476175/3-PDA			0,5-6
2004-1207	CCA	NL6341			0,5-4/6
2004-1207	CSA	154112-1645435			20-10
2004-1207	DNV	E-10423			0,5-6
2004-1207	GL	26187-05HH			0,5-4
2004-1207	KEMA	NL2089139.02			0,5-6
2004-1207	LR	91/20112(E6)			0,5-6
2004-1207	PRS	TE/1718/880590/08			0,5-6
2004-1207	PTB	IECExPTB05.0033U			0,5-6
2004-1207	PTB	PTB05ATEX1095U			0-5-6
2004-1207	RosTest	8189158			0-5-6
2004-1207	UR	E45172			20-10

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected