



The best-seller with an excellent price/performance ratio. It has proven itself a million times in the hands of craftsmen and semi-professionals.

- manufactured according to EN 12413
- complies to oSa regulations
- of course: Made in Germany

A 24 R Characteristics:  
Good service life and fast cutting at a reasonable price.

Field of Application:  
All-purpose disc, suitable for cutting all types of metal.

| Dimensions<br>[mm] | Dimensions<br>[Inch] | Speed<br>[r.p.m.] | Form | Unit<br>pack | Art. No. | EAN<br>[4081600] |
|--------------------|----------------------|-------------------|------|--------------|----------|------------------|
| 100 x 3 x 16       | 4 x 1/8 x 5/8        | 15250             |      | 25           | 1100015  | 100006           |
| 100 x 3 x 16       | 4 x 1/8 x 5/8        | 15250             |      | 25           | 1102015  | 102000           |
| 115 x 3 x 22,2     | 4 1/2 x 1/8 x 7/8    | 13280             |      | 25           | 1110015  | 110005           |
| 115 x 3 x 22,2     | 4 1/2 x 1/8 x 7/8    | 13280             |      | 25           | 1112015  | 112009           |
| 125 x 3 x 22,2     | 5 x 1/8 x 7/8        | 12200             |      | 25           | 1120015  | 120004           |
| 125 x 3 x 22,2     | 5 x 1/8 x 7/8        | 12200             |      | 25           | 1122015  | 122008           |
| 150 x 3 x 22,2     | 6 x 1/8 x 7/8        | 10200             |      | 25           | 1150015  | 130003           |
| 150 x 3 x 22,2     | 6 x 1/8 x 7/8        | 10200             |      | 25           | 1152015  | 132007           |
| 180 x 3 x 22,2     | 7 x 1/8 x 7/8        | 8600              |      | 25           | 1180015  | 140002           |
| 180 x 3 x 22,2     | 7 x 1/8 x 7/8        | 8600              |      | 25           | 1182015  | 142006           |
| 230 x 3 x 22,2     | 9 x 1/8 x 7/8        | 6600              |      | 25           | 1230015  | 150001           |
| 230 x 3 x 22,2     | 9 x 1/8 x 7/8        | 6600              |      | 25           | 1232015  | 152005           |
| 300 x 3,5 x 20     | 12 x 1/8 x 3/4       | 5100              |      | 25           | 1300025  | 160000           |
| 300 x 3,5 x 22,2   | 12 x 1/8 x 7/8       | 5100              |      | 25           | 1300026  | 160017           |