

# Product data sheet

## Characteristics

# VLSH3S7RD

TeSys VLS - pistol handle - screwfix. - red - shaft  
7 mm - 65x65 mm - defeatable

Product availability : Stock - Normally stocked in distribution facility

Price\*\* : 65.07 USD



### Main

Range	TeSys
Device short name	VLSH
Product or component type	Rotary handle
Range compatibility	TeSys VARIO LS VLS3P
Handle colour	Red
Handle front plate colour	Yellow
Rotary handle padlocking	1 to 3 padlocks 0.16...0.31 in (4...8 mm)
Marking	0 - 1

### Complementary

Fixing mode	By 4 screws
Tightening torque	13.28 lbf.in (1.5 N.m)
Base dimension	75 x 75 mm
Height	2.95 in (75 mm)
Width	2.95 in (75 mm)
Depth	2.72 in (69 mm)
Net weight	0.31 lb(US) (0.14 kg)

### Environment

IP degree of protection	IP66
NEMA degree of protection	NEMA 1 NEMA 4 NEMA 4X

### Ordering and shipping details

Category	21734 - TESYS VLS DISCONNECT SWITCHES
Discount Schedule	CP1
GTIN	00785901576648
Package weight(Lbs)	0.20 kg (0.44 lb(US))
Returnability	Yes

---

Country of origin	IT
-------------------	----

---

**Offer Sustainability**

---

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>

---