

Separator VABD-XA-12-P2

Part number: 8191737

FESTO



Data sheet

 [General operating condition](#)

Feature	Value
Size	12
Pressure-zone division	Ducts 3 and 5
Size of pack	2
Operating pressure	-0.1 MPa ... 0.7 MPa
Operating pressure	-1 bar ... 7 bar
Suitability for vacuum	yes
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Storage temperature	-20 °C ... 70 °C
Product weight	0.5 g
Type of mounting	Can be pressed in manually
Note on materials	RoHS-compliant
Material seals	HNBR
Material housing	PA-reinforced