

Butyl and viton gloves, offering wearers advanced protection against chemical hazards

- **Optimized protection:** Featuring a 0.3mm butyl-viton layer, these AlphaTec® 38-612 industrial gloves offer advanced chemical resistance, protecting against aliphatic, halogenated and aromatic hydrocarbons, as well as concentrated mineral acids
- **Advanced ergonomics:** These hand protection gloves are designed with a naturally curved ergonomic shape, which enhances comfort, ensures dexterity, and makes donning and doffing easier
- **Improved comfort:** Thanks to their soft feel, AlphaTec® 38-612 safety gloves are even more comfortable, facilitating sustained wear

Industries

- Automotive
- Life Sciences
- Chemical
- Emergency Medical Services

Applications

- Inspection, selecting, checking parts
- Loading and unloading of process equipment
- Handling incoming goods
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Unexpected leakages spills or other releases



Previously known as: ChemTek™ 38-612

Key Features

- **0.3mm butyl and viton layer:** Heightened chemical resistance
- **Curved ergonomic shape:** Comfort, dexterity and flexibility
- **Soft feel:** For protective gloves that are easy to don and wear

Vulcanization Chemical Accelerators

- 2-Mercaptobenzothiazole disulfide
- Dipentamethylene thriuram disulfide
- Tetramethylthiuram disulfide

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards



0493

EN388: 2016



1010X

EN ISO 374-1:2016



BCFLSPT

EN ISO 374-5:2016



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec®38-612	Coating Material: Viton / Butyl Polymer	8, 9, 10	300 / 11.8	Black	• 36 pairs in a carton, individually wrapped with insert

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.