



SAFETY DATA SHEET
METAL REPAIR COMPOUND

Page: 1

Compilation date: 15/05/2015

Revision date: 20/08/2019

Revision No: 7

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: METAL REPAIR COMPOUND

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Repair compound, filler, putty

1.3. Details of the supplier of the safety data sheet

Company name: ROCOL

ROCOL House

Swillington

Leeds

West Yorkshire

LS26 8BS

ENGLAND

Tel: +44 (0) 113 232 2700

Fax: +44 (0) 113 232 2740

Email: customer-service@rocol.com

1.4. Emergency telephone number

Emergency tel: +44 (0) 113 232 2600

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Aquatic Chronic 3: H412; Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317

Most important adverse effects: Causes skin irritation. May cause an allergic skin reaction. Causes serious eye irritation.
Harmful to aquatic life with long lasting effects.

2.2. Label elements

Label elements:

Hazard statements: H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H412: Harmful to aquatic life with long lasting effects.

Hazard pictograms: GHS07: Exclamation mark



[cont...]

SAFETY DATA SHEET

METAL REPAIR COMPOUND

Page: 2

Signal words: Warning

Precautionary statements: P264: Wash hands thoroughly after handling.
P273: Avoid release to the environment.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P332+P313: If skin irritation occurs: Get medical advice/attention.
P337+P313: If eye irritation persists: Get medical advice/attention.
P501: Dispose of contents/container to local/national regulations.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

EPOXY RESIN (NUMBER AVERAGE MW <=700)

EINECS	CAS	PBT / WEL	CLP Classification	Percent
500-033-5	25068-38-6	-	Skin Irrit. 2: H315; Eye Irrit. 2: H319; Skin Sens. 1: H317; Aquatic Chronic 2: H411	20-30%

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water. Consult a doctor.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water. Do not induce vomiting. Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: No data available.

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Alcohol resistant foam. Dry chemical powder. Carbon dioxide. Do not use water.

[cont...]

SAFETY DATA SHEET
METAL REPAIR COMPOUND

Page: 3

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS. Refer to section 13 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep away from direct sunlight.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Not applicable.

Respiratory protection: Respiratory protection not required.

Hand protection: Protective gloves. Nitrile gloves.

Eye protection: Safety glasses with side-shields. Ensure eye bath is to hand.

[cont...]

SAFETY DATA SHEET
METAL REPAIR COMPOUND

Page: 4

Skin protection: Protective clothing.

Environmental: No special requirement.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Paste

Colour: Grey

Odour: Barely perceptible odour

Evaporation rate: Negligible

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Insoluble

Viscosity: Non-viscous

Boiling point/range°C: > 35

Melting point/range°C: No data available.

Flammability limits %: lower: No data available.

upper: No data available.

Flash point°C: > 100

Part.coeff. n-octanol/water: No data available.

Autoflammability°C: No data available.

Vapour pressure: <500 Pa 50°C

Relative density: 2.25

pH: No data available.

VOC g/l: No data available.

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: No data available.

10.4. Conditions to avoid

Conditions to avoid: Direct sunlight. Heat.

10.5. Incompatible materials

Materials to avoid: Strong acids. Bases. Amines.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

Section 11: Toxicological information

[cont...]

SAFETY DATA SHEET
METAL REPAIR COMPOUND

Page: 5

11.1. Information on toxicological effects

Toxicity values:

Route	Species	Test	Value	Units
ORAL	RAT	LD50	11400	mg/kg

Relevant hazards for product:

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated
Respiratory/skin sensitisation	DRM	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: No data available.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values:

Species	Test	Value	Units
RAINBOW TROUT (<i>Oncorhynchus mykiss</i>)	96H LC50	2	mg/l
Daphnia magna	48H EC50	1.8	mg/l
ALGAE	72H ErC50	11	mg/l

12.2. Persistence and degradability

Persistence and degradability: Not biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No data available.

12.4. Mobility in soil

Mobility: Non-volatile. Insoluble in water. Absorbed only slowly into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: No data available.

[cont...]

SAFETY DATA SHEET
METAL REPAIR COMPOUND

Page: 6

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: No data available

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

Compiled in accordance with REACH.

Phrases used in s.2 and s.3: H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.