



ASSEMBLED VIEW

- CONTACTS ACCEPT 22-26 AWG RANGE.
- HOUSING: POLYESTER OR NYLON, GLASS FILLED, UL94V-0 RATED, COLOR BLACK.
GROMMETS: PVC, UL94V-0 RATED, COLOR BLACK.
CONTACTS: PHOSPHOR BRONZE.
SHELLS: CARBON STEEL.
CABLE CLAMPS: ZINC.
SCREWS & NUTS: CARBON STEEL.
- CONTACTS: GOLD FLASH FOR A LENGTH OF 3.81[.150] MIN FROM MATING END 2.54µm[.000100] MIN TIN ON OPPOSITE END FOR A LENGTH OF 6.60[.260] MIN, BOTH OVER 0.76µm[.000030] NICKEL ON ENTIRE CONTACT.
SHELLS: 5.08µm[.000200] MIN TIN OVER 1.27µm[.000050] MIN COPPER.
MOUNTING SCREWS & NUTS: 3.81µm[.000150] MIN ZINC, CLEAR CHROMATE COATED.
FILISTER HEAD SCREWS: ZINC, CLEAR CHROMATE COATED.
- CABLE CLAMPS: NICKEL OVER COPPER.

749810-9
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN J.GERACE 22MAR06	TE Connectivity
DIMENSIONS: INCHES		CIK C.ROHDE 22MAR06	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M.WALMSLEY 22MAR06	NAME
0 PLC ± -	1 PLC ± -	108-40011	PRODUCT SPEC
2 PLC ± 0.13 [.005]	3 PLC ± -	114-40003	APPLICATION SPEC
4 PLC ± -	ANGLES ± -	SIZE	CAGE CODE
MATERIAL	FINISH	100779	DRAWING NO
		A1	749810-9
		CUSTOMER DRAWING	RESTRICTED TO
		SCALE 3:1	SHEET 1 OF 1
			REV A1