

TUFF-T2000

HIGH POWERED 2K LUMEN RECHARGEABLE LED WORK LIGHT



2 BRIGHTNESS LEVELS

2000 | 1000 LUMENS



UP TO 14HR RUNTIME

2000 LUMEN 7HR
1000 LUMEN 14HR

ADJUSTABLE STAND WITH HANGING BRACKET



BATTERY INDICATOR 18 V / 14 V



POWER ON / OFF ON / OFF CLICK TO DIM



POWER TAKE OFF BY USB



SPLASH & DUSTPROOF RATED IP44



TRIPOD MOUNTABLE

POWER TOOL ADAPTORS

4-IN-1 OR 5-IN-1 POWER OPTIONS



4-IN-1 ADAPTER

BOSCH
MAKITA
HITACHI
PANASONIC



5-IN-1 ADAPTER

DEWALT
METABO
MILWAUKEE
MAFELL
CAS

TECHNICAL DATA

LUMEN:	2000 1000
RUNTIMES:	7hrs @ 2000 lumens 14hrs @ 1000 lumens
BATTERY POWER:	18V 5Ah
USB OUTPUT:	5V 1Ah
WEATHERPROOF:	IP44 dust & water resistant
FUNCTIONS:	2 light levels - 100% 50%, adjustable stand, hanging hook, tripod mountable
SIZE:	361 x 237 x 182 mm
WEIGHT:	
MATERIAL:	ABS body, TPE surround
WARRANTY:	2 Years

KIT OPTIONS:

TUFF-T2000 with built in:

4 in 1 Adapter for Makita,
Bosch, Hitachi & Panasonic
User Manual

OR

5 in 1 for DeWalt, Metabo,
Milwaukee, Mafell & CAS
User Manual

0800 292 2188

tradetuff.co.uk

info@tradetuff.co.uk

TRADE TUFF