



Datasheet

Stock No: 263-6005

RS Pro 30 W Servo Motor, $24 \rightarrow 30 \text{ V}$ dc, 14Ncm, 1600 rpm



Product Details

Servo Motor Fitted with Tacho

Fitted to servo motor (stock no. 263-5995) an integral dc tachogenerator to provide accurate velocity control, in applications which require smooth operation over a wide speed range

This motor is intended to be used with linear dc servo amplifier





Specifications

Maximum Output Torque	36 Ncm
Supply Voltage	$24 \to 30 \ \forall \ dc$
Output Speed	1600 rpm
Power Rating	30 W
Stall Torque	14Ncm
Shaft Diameter	6mm
Length	134mm
Width	66mm