

LU9GC7

TeSys U profibus DP power supply module LU9 G - for TeSysU starter-controllers

Main

Range of product	TeSys U
Device short name	LU9G
Product or component type	Profibus DP power supply module
Product compatibility	LULC07

Complementary

[Us] rated supply voltage	24 V DC
Maximum current I _{rms}	≤ 1.5 A
Width	45 mm
Height	170 mm
Depth	65 mm

Environment

RoHS EUR conformity date	4Q2009
RoHS EUR status	Will be compliant

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.