



SIVACON, door half, left, with ventilation openings, IP20, H: 1800 mm, W: 600 mm, RAL 7035, protection class 1

Model		
product brand name	SIVACON	
product designation	Door half	
design of the product	With ventilation openings	
design of the surface	Powder-coated	
design of the product EMC version	No	
Protection class		
protection class IP	IP20	
operating resource protection class	safety class 1	
Appearance		
RAL color number	7035	
color	light grey	
Product details		
product component		
• ventilation	Yes	
• viewing door	No	
• door for disconnecter lock	No	
Mechanical Design		
height	1 800 mm	
width	600 mm	
opening direction of the door	left	
net weight	17 kg	
material	steel	
Approvals Certificates		
General Product Approval	Test Certificates	other



[Special Test Certificate](#)

[Confirmation](#)

[Miscellaneous](#)

[Miscellaneous](#)

Environment

Siemens
EcoTech



[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MF1860-2UT25-1BA2>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MF1860-2UT25-1BA2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MF1860-2UT25-1BA2

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

4/13/2025 

