



Part Number : [936010450](#)

Product Description : Heavy-Duty Crimp Contact Insert, Male, 17-Pole, 10A, for Turned and Stamped Crimp Contacts, Size QD

Series Number : 93601

Status : Active


Product Category : Heavy-Duty Connectors

Engineering Number : 7617.5911.0

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006 
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Crimp Contact Insert, Male, 17-Pole, 10A, for Turned and Stamped Crimp Contacts, Size QD
Component Type	Inserts - Crimp Contact
Insert Series	S-QD17
Product Name	Heavy-Duty Connectors
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191891088

Agency

CSA	256883
UL	E249674

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	250V

Physical

Component Size	QD
Durability (mating cycles max)	500
Gender	Male
Insert Color	Grey
Material - Insert	Polycarbonate
Net Weight	15.000/g
Number of Rows	5
Packaging Type	Bag

Polarized to Mating Part	Yes
Poles	17
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Heavy-Duty Crimp Contact Insert, Female, 17-Pole, 10A, for Turned and Stamped Crimp Contacts, Size QD	<u>936010449</u>

Use with Part(s)

Description	Part Number
Use With	Turned (14-26 AWG) and Stamped (16-26 AWG) Contacts - Male