

Click-Torque X 5 torque wrench for insert tools, 14 x 18 mm, 60 - 300 Nm  
Torque wrench 60-300 Nm



EAN	4013288193810	Dimension:	600x60x60 mm
Code:	05075655001	Weight:	1439 g
Article-No.		Country of origin:	TW
		Customs tariff no.:	82041100

- For 14x18 mm interchangeable insert tools
- Measuring range: 60-300 Nm; Precise to +/- 3% as per DIN EN ISO 6789-1:2017-07
- Easy setting and saving of the desired torque value with audible and tactile clicks when reaching the scale values
- Audible and tactile release mechanism when the set torque value is reached
- Very robust design with ergonomic 2-component handle suitable for right-hand use

Click-Torque wrench in the unmistakable, robust Wera design with high accuracy as per DIN EN ISO 6789-1: 2017-07. Easy setting and saving of the default value. The audible and tactile clicks on reaching the scale values also facilitate the safe setting of the desired torque value. The robust release mechanism guarantees a clearly audible and tactile release signal when the set torque is reached. For right and left-hand use and with square insert 14x18mm for insert tools.