

## Projector Table

00077510 Projector Table with 2 Levels (42 x 50 / 40 x 35 cm), Height-Adjustable, wi



### Highlightstext:

- Projection table for the precise alignment of the projector with the screen, with second platform for perfect presentations
- Dynamic presentations: with two highly flexible platforms that can be adjusted in terms of height, inclination and orientation, you can direct your projector presentation perfectly for your audience
- Flexible use of the two platforms: for projectors and the lower level as a working surface, e.g. for a notebook and documents
- Upper platform: 42 x 50 cm, load capacity: up to 10 kg, steplessly height-adjustable: min. 85 - max. 110 cm, tilt -35° - + 35°
- Lower platform: 40 x 35 cm, load capacity: up to 10 kg, steplessly height-adjustable: min. 70 - max. 95 cm, tilt -35° - + 35°
- Both levels can be rotated around 360°
- The stable limiter on both tables give the projector and laptop a secure grip (useful surface with limiters: upper platform 36 x 45 cm, lower platform 36.5 x 29.5 cm)
- The projection table is especially stable and robust thanks to the steel star foot
- With the projector cart featuring 4 smooth-running swivel castors, you remain mobile and can therefore use the projector in different rooms
- 2 castors can be locked in position so that your equipment remains safely where it should

### Technical characteristics:

- Colour: Black
- Product Division: Photo & Video
- Shade of colour: Black
- Maximum Load: 10 kg

### Delivery:

- 2 tabletops
- 1 mounting pillar
- 1 star foot
- 4 castors
- Mounting set

 4 007249 775108	Brand	Item-no.	VE	MB	SRP
	<b>hama</b>	00077510	1	1	EUR 99,00