

SMA-A0102FTDL2K2

✓ ACTIVE

Neohm | Neohm SMA-A

TE Internal #: 5-2176314-1

2.2K ohm, Surface Mount Precision Resistor, Thin Film, 0102, .3 W, 1

%, ±50 ppm/°C, Metal Electrode Leadless Face (MELF), 2

Terminations, Neohm SMA-A

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistance Value: 2.2K Ω

Resistor Type: Precision Resistor

Element Type: Thin Film

Package Size Code: 0102

Power Rating: .3 W

Features

Product Type Features

Resistor Type	Precision Resistor
Element Type	Thin Film
Package Size Code	0102

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	200 V
Resistance Value	2.2K Ω
Power Rating	.3 W
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Metal Electrode Leadless Face (MELF)
Number of Terminations	2

Dimensions

Product Diameter	1.1 mm[.043 in]
Product Length	2.2 mm[.087 in]

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±50 ppm/°C

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

SMA-A0102FTDL2K2

2.2K ohm, Surface Mount Precision Resistor, Thin Film, 0102, .3 W, 1 %, ±50 ppm/°C, Metal Electrode Leadless Face (MELF), 2 Terminations, Neohm SMA-A



TE Part # 9-2176316-4
MELF SMA-A 330K 1% 50PPM 0207 1W

TE Part # 3-2176315-2
MELF SMA_A 39K 0.1% 15PPM 0204 0.4W

TE Part # 9-2176315-8
MELF SMA-A 1M0 1% 50PPM 0204 0.4 W

TE Part # 2176316-5
MELF SMA_A 220R 0.1% 15PPM 0207 1W

TE Part # 6-2176314-9
MELF SMA-A 10R 1% 50PPM 0102 0.3 W

Also in the Series | Neohm SMA-A

Surface Mount Resistors(270)

Customers Also Bought

TE Part #2-2176481-5
RA73F 1J 10K5 0.1% 5K RL

TE Part #224920-E
MICROS STV 9 407 188 * 0007 J 3 224920 M

TE Part #2-1827875-0
DYNAMIC 1200D HDR ASSY V 20PY BLACK GOLD

TE Part #D841073001
55D0214-24-9

TE Part #2-1827864-0
DYNAMIC 1200D REC HSG 20P Y BLACK

TE Part #1-179276-2
DYNAMIC 3200 HDR ASSY 2P H


TE Part #1614923-1
CPF0805 36K 0.1% 25PPM 1K RL

TE Part #214915-E
MSPPM 5 F SMDTHR F10 * A V 137 094 * E00


SMA-A0102FTDL2K2

2.2K ohm, Surface Mount Precision Resistor, Thin Film, 0102, .3 W, 1 %, ±50 ppm/°C, Metal Electrode Leadless Face (MELF), 2 Terminations, Neohm SMA-A





TE Part #214916-E
MSPPM 5 M SMDTHR M1 * A V 137
094 * E008



TE Part #2176316-9
MELF SMA_A 470R 0.1% 15PPM 0207
1W

Documents

Product Drawings

MELF SMA_A 2K2 1% 50PPM 0102 0.3W

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-2176314-1_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-2176314-1_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-2176314-1_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMA-A-1017

English