


C20A, Film, Metallized Polypropylene, AC Filter, 22 uF, 10%, 1000 VAC, 2300 VDC



General Information

Supplier:	KEMET
Series:	C20A
Dielectric:	Metallized Polypropylene
Style:	Can
Features:	Single Phase PFC
RoHS:	Yes
Lead:	Threaded Studs M10
Miscellaneous:	Thermal Resistance = 8.0 C/W

Dimensions

D	75mm +/-0.5mm
L	147mm +/-2mm
W	21mm +/-1mm
S	35mm +/-1mm

Packaging Specifications

Mounting:	Bolt - M12x16
Packaging:	Bulk, Bag

Specifications

Capacitance:	22 uF
Capacitance Tolerance:	10%
Voltage AC:	1000 VAC
Voltage DC:	2300 VDC
Temperature Range:	-25/+70C
Rated Temperature:	70°C
Insulation Resistance:	10 MOhms
Max dV/dt:	85 V/us
Resistance:	2 mOhms (10kHz)
Ripple Current:	35 Amps (10kHz 40C)
Inductance:	155 nH