



Hovedbryter, 4p, 400V, 100A

Type IS-100/4
Catalog No. 276285
Alternate Catalog No. IS-100/4
EL-Nummer 0001460857

Illustrasjon lik

Leveringsprogram

Grunnfunksjon			Hovedlastbryter
Poler			4-polet
Bruk			Koblingsenheter for industriell bruk og hevet funksjonelt bygg
Nominell strøm	I_n	A	100
Sortiment			IS
Koblingsymboler			

Data for konstruksjonsdokumentasjon iht. IEC/EN 61439

Tekniske data for konstruksjonsdokumentasjon			
Nominell strøm for angivelse av tapseffekt	I_n	A	100
Tapseffekt per pol, strømvhengig	P_{vid}	W	3.9
Tapseffekt for driftsmiddelet, strømvhengig	P_{vid}	W	11.8
Tapseffekt statisk, uavhengig av strøm	P_{vs}	W	0
Avleveringskapasitet for tapseffekt	P_{ve}	W	0
Omgivelsestemperatur ved drift min.		°C	-5
Omgivelsestemperatur ved drift maks.		°C	40

Tekniske data etter ETIM 6.0

Devices for distribution board-/surface mounting (EG000062) / Main switch for distribution board (EC001545)			
Electric engineering, automation, process control engineering / Electrical installation, device / Modular serial built-in device for electrical circuit distributors / Main switch for distribution board (ecl@ss8.1-27-14-23-01 [AFZ813011])			
Switching function			Other
Number of normally open contacts			0
Number of normally closed contacts			0
Number of change-over contacts			0
Number of poles			4
Nominal rated current		A	100
Nominal rated voltage		V	240
Min. rated voltage		V	240
Rated switching capacity		kA	0
Short-circuit breaking capacity (Icw)		kA	2
Voltage type			AC
Forced segregation (according to DIN VDE 0113)			No
With signal lamp			No
Colour calotte			Not applicable
Lamp type			Not applicable
Lamp socket			Not applicable
Max. lamp power		W	0
Width in number of modular spacings			4
Built-in depth		mm	69.5

Dimensjoner

