



LED Ba9s T10x25 HO 24V-28V AC/DC 0.4W 25lm White

Article number: 146537

BAI Miniature Single LED Ba9s Buis 10x25mm 24V-28V AC/DC 16mA 0.016A 0.4W White 3000K 30000h

In view of the call for more sustainable products, a large part of the traditional miniature and signaling lamps is now also available in LED.

General ETIM properties

ETIM group	Lamps
ETIM class	Indication- and signalling lamp
Name	LED Ba9s T10x25 HO 24V-28V AC/DC 0.4W 25lm White
Brand	Bailey
Productseries	Miniature LED
Producttype	Ba9s

ETIM specifications

Socket	BA9s
Lamp voltage [V]	24 - 28
Nominal current [mA]	16
Lamp power [W]	1 - 1
Diameter [mm]	10
Total length [mm]	25
Lamp shape	Tube, single-ended
Technology	LED
Luminous flux [lm]	25
Halogen	No
Krypton	No
Xenon	No
Colour	White
Colour temperature [K]	3000
Suitable for torches	No
Suitable for pointer	No
Suitable for round flashing luminaire	No
Average nominal lifetime [h]	30000
Energy efficiency class according to EU regulation 2019/2015	G

Alternative articles



LB2401C28W

LED Ba9s T10X24 White 24V-28V AC/DC