



Model: **TEAK** **Protection Class:** **S3 SRC ESD**
Article: **RR10304** **EU Regulations:** **EN ISO 20345:2011**

DESCRIPTION

Ankle boots safety shoes totally "metal free", u power comfortable and light of the "Rock & Roll" range, with soft full-grain leather upper, water-repellent, tip protection in anti-abrasion MATRIX, inserts in breathable mesh, tip AirToe Composite, antiperforation, anti-slip and PU / PU sole, S3 SRC ESD

UPPER

Full grained water resistant leather, with abrasive resistant Bay-Cast protection

LINING

WingTex air tunnel textile lining material

SAFETY TOE CAP

AirToe Composite perforated safety toe cap with breathable membrane

PIERCE-RESISTANCE

Save & Flex PLUS

FOOTBED

WOW

INTERSOLE

Soft P.U. comfort inner layer

SOLE

Antislip, antistatic and hard wearing P.U.

FIT

Natural Confort 11 Mondopoint

SIZE

35-48 (UK: 2-13)

