


Product selected: Sylproof Superia PC T5 16mmØ 1x14W lamp with A2 ballast

Moisture proof diffuser luminaire. Housing made of polycarbonate. Colour light grey. With top and fitting end cut outs for mains supply and further wiring as well as for through wiring by means of heat resistant internal wiring. Injection mulded diffuser with internal prism for even lighting distribution. Diffuser fixed to the body by using stainless steel clips. Inject gasket for high IP rate. Aluminium reflector. Gear tray made of steel, saved by maintenance cord. D-Mark for electronic ballast version. Polyurethane seal gasket

Product Image



Product Line Drawing



Lamp	L	I	H	F
1 x 18/14/24 - 2x14/24	662	92	99	400
1 x 36/28/54 - 2x28	1285	92	99	900
1 x 58/55/49/90 - 2x35/49	1565	92	99	930
1 x 70	1865	92	99	1026
2 x 18	662	137	99	400
2 x 36/54	1285	137	99	900
2 x 58	1565	137	99	930
2 x 70	1865	137	99	1026

Lamp(s)



Certifications



Product Details

Order code	0056195
Item name	Sylproof Superia PC T5 16mmØ 1x14W lamp with A2 ballast
Mounting	Ceiling pendant, Ceiling surface
Technical description	Polycarbonate body & diffuser. Stainless steel fixing
Place of use	Interior
Colour	Grey
Length (mm)	662
Width (mm)	92
Height (mm)	99
Weight (kg)	1.2
Housing	Polycarbonate
Shock resistance	2 J
Distribution type	Symmetric
Diffuser finish	Prismatic
Diffuser material	Polycarbonate
LOR (%)	67%
Reflector finish	Aluminium
Reflector material	Polycarbonate
Lamps description	1 x 14W T16 G5
Lamp included	No
Number of heads	1
Control gear availability	Included
Control gear type	Electronic
Control gear description	Electronic ballast with reduced losses
Control gear mounting	Integral
T Class Max	25°C
T Class Min	0°C
Voltage (V)	220-240