

CD COVER 80 WH - Cover profile

3240649

<https://www.phoenixcontact.com/gb/products/3240649>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover for cable duct, white, width: 80 mm, length: 2000 mm

Commercial data

Item number	3240649
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE7433
Product key	BE7433
Catalog page	Page 555 (C-5-2015)
GTIN	4046356629751
Weight per piece (including packing)	556 g
Weight per piece (excluding packing)	490 g
Customs tariff number	39259020
Country of origin	DE

CD COVER 80 WH - Cover profile

3240649

<https://www.phoenixcontact.com/gb/products/3240649>



Technical data

Product properties

Product type	Cover
--------------	-------

Dimensions

Width	80 mm
Height	2000 mm
Depth	11 mm
Length	2000 mm

Material specifications

Color	white (RAL 9010)
Material	PVC
Flammability rating according to UL 94	V0
Components	Lead-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
---------------------------------	------------------

CD COVER 80 WH - Cover profile

3240649

<https://www.phoenixcontact.com/gb/products/3240649>



Classifications

ECLASS

ECLASS-13.0	27400776
-------------	----------

ETIM

ETIM 9.0	EC000727
----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

CD COVER 80 WH - Cover profile



3240649

<https://www.phoenixcontact.com/gb/products/3240649>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk