

# Pneum. contact metal OD 3 female+valve



| Part number        | 09 14 000 6463                          |
|--------------------|---|
| Specification      | Pneum. contact metal OD 3 female +valve |
| HARTING eCatalogue | https://b2b.harting.com/09140006463     |

#### Identification

| Category                   | Contacts               |
|----------------------------|------------------------|
| Type of contact            | Pneumatic contact      |
| Description of the contact | With shut-off Straight |

#### Version

| Gender | Female |  |
|--------|--------|--|
|--------|--------|--|

### Technical characteristics

| Limiting temperature | -20 +85 °C |
|----------------------|------------|
| Operating pressure   | ≤10 bar    |
| Tube outer diameter  | 3 mm       |

## Material properties

| Material (contacts)         | Brass  |
|-----------------------------|--|
| Material (seal)             | NBR  |
| RoHS                        | compliant with exemption                               |
| RoHS exemptions             | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                  | compliant with exemption                               |
| China RoHS                  | 50   |
| REACH Annex XVII substances | No   |
| REACH ANNEX XIV substances  | No   |
| REACH SVHC substances       | Yes  |



## Material properties

REACH SVHC substances Lead

## Specifications and approvals

| UL / CSA | UL 1977 ECBT2.E235076             |
|----------|-----------------------------------|
| UL / CSA | CSA-C22.2 No. 182.3 ECBT8.E235076 |

#### Commercial data

| Packaging size                 | 10   |
|--------------------------------|--|
| Net weight                     | 11 g                                       |
| Country of origin              | Germany                                    |
| European customs tariff number | 39269097                                   |
| eCl@ss                         | 27440204 Contact for industrial connectors |