

重量：約42g



HDMIポートとSD・microSDカードスロットを搭載したUSB Type-Cハブ。

USB-5TCHC26BK

HDMIポート付 USB Type-Cドッキングハブ

JANコード 4969887784099



仕様

PC接続端子

コネクタ形状	USB Type-C
対応規格	USB 5Gbps (USB3.2 Gen1/3.1 Gen1/3.0) 準拠 ※USB5GbpsはUSB-IF (USB Implementers Forum) によりUSB3.2/3.1/3.0が名称変更されたもので同じ規格です。
ケーブル長	15cm
ケーブルタイプ	ケーブル一体型

USBポート

ポート数	3ポート
最大データ転送速度	5Gbps (理論値)
USB Type-Cメス/USB 2.0	1ポート
USB Aメス/USB 5Gbps	1ポート
USB Aメス/USB 2.0	1ポート
供給電流	最大3000mA (全ポート合計) ※接続する機器の消費電流が本製品の供給電流を超える場合、バスパワーで正常に動作しない場合があります。

電源

電源供給方式	バスパワー
--------	-------

映像出力ポート

対応出力ディスプレイ数	1台
最大対応解像度	4K/30Hz

最大対応解像度/リフレッシュレート	3840×2160 ※記載の対応解像度はご使用のパソコンがDisplayPort Alt Mode（DP1.4以上）に対応している必要があります。
HDCP	1.4
HDMI	1ポート

カードリーダー

スロット	SDメモ리카ード、microSDカード
対応メディア規格	SDXC、SDHC、SD、microSDXC、microSDHC、microSD
最大対応メディア	SDカード/2TB microSDカード/2TB

共通仕様

セット内容	※取説はWEBのみです。
サイズ	約W25×D12×H132mm
重量	約42g

特長

HDMI出力ポート付のスリムUSBType-Cハブです。

SD・microSDスロット搭載でメモリーカードの読み書きができます

HDMI出力4K/30Hz対応で、ソフトウェアのインストールなしで簡単にマルチディスプレイ環境（ミラーモード/拡張モード）を実現できます。

USB Type-Cコネクタ採用で、Type-Cポートを搭載したパソコンなどで使用できます。

USB5Gbpsポートからのノイズを受けにくい、入力機器の接続に適したUSB2.0ポートを搭載しています。

《制限事項》

※本製品はパソコン本体のType-Cポートに直接接続してください。USBハブ、増設のUSBポートではご利用いただけません。

※本製品の取り外し、接続に関して、基本的にプラグアンドプレイには対応していますが、まれにUSB認識のタイミングエラーにより正常に表示しない、動作しない場合があります。再度抜き差しをお試しください。これは本製品の不具合、故障ではありません。

※本製品はWindows OS、Mac OSが動作している状態で使用するものです。システム起動時や、BIOS画面では動作（表示）しません。

※対応機種、対応接続機器・環境の場合であっても正常に動作しないことがあります。

※USB2.0/1.1規格の製品を接続する場合、最大転送速度は遅い方の規格になりますので、ご注意ください。

※全てのUSB Type-C機器に接続、動作を保証できるものではありません。

※本製品はUSB 5Gbps（3.2 Gen1）規格に対応しておりますが、USB 5Gbps（3.2 Gen1）の規格値（5Gbps）の転送速度は規格値です。

USB Type-C hub with HDMI port and SD/microSD card slots. USB-5TCHC26BK

Specifications

PC Connection Terminal

- ・ Connector Shape : USB Type-C
- ・ Compatible Standard : USB 5Gbps (USB 3.2 Gen1/3.1 Gen1/3.0)
※USB 5Gbps is the same standard as USB 3.2, 3.1, and 3.0, renamed by the USB-IF (USB Implementers Forum).
- ・ Cable Length : 15cm
- ・ Cable Type : Integrated Cable

USB Ports

- Number of Ports : 3
- Maximum Data Transfer Speed : 5Gbps (Theoretical)
- USB Type-C Female/USB 2.0 (1 port)
USB A Female/USB 5Gbps (1 port)
USB A Female/USB 2.0 (1 port)
- Supply Current : Maximum 3000mA (Total of all ports)
※If the current consumption of the connected device exceeds the supply current of this product, it may not function properly when bus-powered.

Power

- Power Supply Method: Bus-powered

Video Output Port

- Number of Supported Output Displays : 1
- Maximum Supported Resolution : 4K/30Hz
- Maximum Supported Resolution/Refresh Rate : 3840x2160
※The listed supported resolutions require your computer to support DisplayPort Alt Mode (DP1.4 or higher).
- HDCP : 1.4
- HDMI : Port 1

Card Reader

- Slots : SD Memory Card, microSD Card
- Supported Media Formats : SDXC, SDHC, SD, microSDXC, microSDHC, microSD
- Maximum Supported Media : SD Card/2TB
microSD Card/2TB

Common Specifications

- Set Contents : ※Instruction manual available online only.
- Dimensions : Approx. 25mm W x 12mm D x 132mm H
- Weight : Approx. 42g

Features

- This is a slim USB Type-C hub with an HDMI output port.
- It features SD and microSD slots for reading and writing memory cards.
- It supports 4K/30Hz HDMI output, allowing you to easily create a multi-display environment (mirror mode/extended mode) without installing any software.
- The USB Type-C connector allows it to be used with computers equipped with Type-C ports.
- It also features a USB 2.0 port that is less susceptible to noise from USB 5Gbps ports and is ideal for connecting input devices.