

FLUKE®

411D Laser Distance Meter



Compact, easy to use distance meter for indoor and outdoor usage

- Large LCD display and shortcut buttons for one handed operation
- Easy to use point and shoot design
- Instant measurement with one-button operation
- Easy targeting with bright laser
- Quick calculation of area and volume
- Easy addition and subtraction of measurements
- Automatic shut-off feature
- Pythagoras calculation
- Carry Pouch

Two-year manufacturers warranty

Technical specification	
Range (for extended distances, use a target plate):	0.1 m to 30 m
Measuring accuracy:	± 3 mm
Units displayed:	00.000 m
Laser class:	II
Laser type:	635 nm, < 1 mW
Automatic power off:	after 180 seconds
Battery life:	up to 3,000 measurements
Pythagoras (Indirect measurement):	Simple
Ingress protection:	IP40
Dimensions:	123 mm x 50 mm x 26 mm
Weight:	150 g (5.29 oz)
Temperature range:	
Storage	-25 °C to 70 °C
Operation	0 °C to 40 °C
Operating altitude (ISO 9022):	up to 3500 m
Storage humidity (at 35 °C):	maximum 85 % for 24 h
Batteries:	AAA (2)

411D

579-165