

ELASTECH

IDP100x30-8 HL45

EAN 4031582460650

Wheel centre made of Aluminium, Tread: heat resisting synthetic material, damping, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	100 mm
Wheel width	30 mm
Axle Hole-Ø	8 mm
Hub length	45 mm
Temperature	-30/+280 °C
Weight	0.294 kg
Hardness of tread	Shore A 80
Load capacity	200 kg
Load capacity (static)	400 kg

Advantages at a glance

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ○ ○ ○