



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #4-1879378-1
TLR 2512 2.0W R0025 1% 150PPM 2K RL

TE Part #1768020-5
ESW30-025

TE Part #3-2176217-5
CPF A 0805 1K5 0.1% 25PPM 1K RL

TE Part #6-1879207-8
RN 0603 499K 0.1% 10PPM 5K RL

TE Part #3-2176230-4
3522 470R 5% 3W

TE Part #4-1393224-6
RY211012

TE Part #CAT-C339-SQ1
Wirewound Resistor: Vertical Mount

TE Part #1-1623932-7
CFR50 5% 12K

TE Part #3-2176345-4
CRGCQ 1210 5K6 1%

Documents

Product Drawings

9P,RAST 2.5 Tab Header,Ex- Locking,THV

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-1971817-9_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-1971817-9_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-1971817-9_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[RAST Connector System Catalog](#)

English

[7-1773465-3_RAST2.5_Flyer](#)

English

[Product Specifications](#)

[Product Specification](#)

English

[Agency Approvals](#)

[VDE Certificate](#)

English