

CA-12S2N8A8007X - Cable connector



1244523

<https://www.phoenixcontact.com/in/products/1244523>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: CA, straight, shielded: yes, Screw locking mechanism, No. of pos. : 12, Direction of rotation: Counter direction, contact connection type: Socket, Crimp connection, cable diameter range: 6 mm ... 10 mm, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Commercial data

Item number	1244523
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ABRAEA
GTIN	4063151407162
Weight per piece (including packing)	92.2 g
Weight per piece (excluding packing)	88.7 g
Customs tariff number	85366990
Country of origin	DE

CA-12S2N8A8007X - Cable connector



1244523

<https://www.phoenixcontact.com/in/products/1244523>

Technical data

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Direction of rotation	Counter direction
-----------------------	-------------------

Insulating body

Note	Order information: Order crimp contacts Ø 1 mm separately
Coding	N
Insulation body material	PA 6.6
Connection method	Crimp connection
Contact switching type	Socket
Application	Signal
Number of positions	12
Direction of rotation	Counter direction
Connection profile	12
Contact diameter	1 mm
Power contacts	
Rated current	8 A
Rated voltage	48 V AC 74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3

Housing

Housing material	Turned parts: copper zinc alloy (CuZn), die-cast parts: zinc (GD-Zn)
Type of locking	Screw locking mechanism
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

Seal

External cable diameter	6 mm ... 10 mm
Seal material	NBR

Environmental and real-life conditions

Ambient conditions

Ambient temperature (storage/transport)	15 °C ... 25 °C
Permissible humidity (storage/transport)	50 % ... 65 %

CA-12S2N8A8007X - Cable connector


1244523

<https://www.phoenixcontact.com/in/products/1244523>



Drawings

Schematic diagram



Contact chamber numbering (view of plug-in side), socket counter direction

CA-12S2N8A8007X - Cable connector



1244523

<https://www.phoenixcontact.com/in/products/1244523>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1244523>

cUL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	4 A	20	-

UL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	48 V	6 A	20	-

cULus Recognized				
------------------	--	--	--	--

CA-12S2N8A8007X - Cable connector



1244523

<https://www.phoenixcontact.com/in/products/1244523>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

CA-12S2N8A8007X - Cable connector



1244523

<https://www.phoenixcontact.com/in/products/1244523>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

CA-12S2N8A8007X - Cable connector



1244523

<https://www.phoenixcontact.com/in/products/1244523>

Accessories

CA-Z0077X - Metal protective cap

1245447

<https://www.phoenixcontact.com/in/products/1245447>



Metal protective cap, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

SF-Z0028 - Torque screwdriver

1607456

<https://www.phoenixcontact.com/in/products/1607456>



Torque screwdriver, series: RC, UC, SH, SF

CA-12S2N8A8007X - Cable connector

1244523

<https://www.phoenixcontact.com/in/products/1244523>



SF-Z0027 - Hook wrench

1607455

<https://www.phoenixcontact.com/in/products/1607455>



Hook wrench, series: RC, UC, RF, SF

RF-Z0014 - Color coding

1620588

<https://www.phoenixcontact.com/in/products/1620588>



Color coding, color: green

CA-12S2N8A8007X - Cable connector

1244523

<https://www.phoenixcontact.com/in/products/1244523>




RF-Z0015 - Color coding

1620592

<https://www.phoenixcontact.com/in/products/1620592>

Color coding, color: orange



RF-Z0016 - Color coding

1620593

<https://www.phoenixcontact.com/in/products/1620593>

Color coding, color: black



CA-12S2N8A8007X - Cable connector

1244523

<https://www.phoenixcontact.com/in/products/1244523>



RC-22S2000 - Crimp contact

1603327

<https://www.phoenixcontact.com/in/products/1603327>



Crimp contact, Socket, rolled, Single contact, contact diameter: 1 mm, crimp range: 0.22 mm² ... 0.56 mm², Single contact, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

RC-10KS0,08-0,56 - Crimp contact

1241093

<https://www.phoenixcontact.com/in/products/1241093>



Crimp contact, Socket, turned, Single contact, contact diameter: 1 mm, crimp range: 0.08 mm² ... 0.56 mm², Contact release tool not necessary for the 12- and 17-pos. crimp versions of the M23-PRO series, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

CA-12S2N8A8007X - Cable connector

1244523

<https://www.phoenixcontact.com/in/products/1244523>



RF-Z0003X - Square mounting flange

1242369

<https://www.phoenixcontact.com/in/products/1242369>



Square mounting flange, Axial seal, 4xM3, flange dimensions: 35 mm x 35 mm, series: RF, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

PROT-M23-SG-IT-IP20 - Plastic protective cap

1577206

<https://www.phoenixcontact.com/in/products/1577206>



Plastic protective cap, M23, series: CA, RC, RF, UC, RM

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in