

FR11 - FR Modaflame Anti-Static Long Sleeve T-Shirt

Collection: Modaflame™ Knit

Range: Flame Resistant Multi-Norm

Shell Fabric: Modaflame Knit: 60% Modacrylic, 39% Cotton, 1% Carbon Fibre 200g

Product information

High quality construction and premium materials set this Flame-Resistant Anti-Static Long Sleeve T-Shirt aside from its competitors.

Standards

EN ISO 11612 (A1, B1, C1, F1)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 4.4 CAL/CM², EBT 5.5 CAL/CM²)

IEC 61482-2 IEC 61482-1-2 APC 1

ASTM F1959/F1959M-12 (EBT = 4.3 CAL/CM² (HAF = 66%))

Modaflame™ Knit

Constructed from an inherently fire resistant yarn of 60% Modacrylic, 39% Cotton and 1% Carbon Fibre. Tested to meet and adhere to the required EN Standards, Modaflame™ Knit is strong, durable and highly innovative.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Features

- Inherent flame resistant qualities will not diminish with washing
- Protection against radiant, convective and contact heat
- Flame resistant ribbed cuff for added safety
- High cotton content for superior comfort
- Ribbed cuffs for added comfort
- Outstanding colour fastness and shrinkage results





PRODUCT SPECIFICATION & TECHNICAL DATASHEET

FR11 - FR Modaflame Anti-Static Long Sleeve T-Shirt Commodity Code: 6109909000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
Bracetown Business Park
D15 YN2P, Ireland
Cert No: 2777_13282_05_E00_00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
FR11BKRS	Black	55.0	36.0	42.0	0.3600	0.0832	5036108245505	25036108734003
FR11BKRM	Black	55.0	36.0	42.0	0.3800	0.0832	5036108245499	25036108733990
FR11BKRL	Black	55.0	36.0	42.0	0.4000	0.0832	5036108245482	25036108733983
FR11BKRXL	Black	55.0	36.0	42.0	0.4200	0.0832	5036108245512	25036108734010
FR11BKRXXL	Black	55.0	36.0	42.0	0.4400	0.0832	5036108245529	25036108734027
FR11BKRXXXL	Black	55.0	36.0	42.0	0.4600	0.0832	5036108245536	25036108734034