

## Features

- Manufactured with Bi-metal flexible spring steel for long life and excellent cutting performance.
- Shatterproof & flexible with hardened teeth for maximum wear resistance and are suitable for cutting a wide range of materials.

## 300mm Hacksaw Blades 18TPI (10pc)

RS Stock No.: 0757844



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### RS PRO Hacksaw Blade

Hacksaw Blades are manufactured with Bi-metal flexible spring steel for long life and excellent cutting performance. The blades are shatterproof & flexible with hardened teeth for maximum wear resistance and are suitable for cutting a wide range of materials.

- *Suitable for use with most Hacksaws*
- *Suitable for use on Metal, Stainless Steel, Plastic, Wood, Aluminium*
- *Shatterproof*

## General Specifications

<b>Material Code</b>	D6AM2
<b>Type</b>	Hacksaw Blade
<b>Blade Body Thickness</b>	0.62mm
<b>TPI</b>	18
<b>Heat Treatment (Yes/No)</b>	Yes
<b>Heat Treatment Technology</b>	Vacuum Furnace Heat Treatment
<b>Blade Finishing Technology</b>	Black Paint
<b>Teeth Technology</b>	Milled Teeth
<b>Working Length</b>	300mm

Stock No.	Material Code	TPI	Working Length	Teeth Technology
XXX-XXXX 0757843	D6AM2	24	150mm	Milled Teeth
XXX-XXXX 0757844	D6AM2	18	300mm	Milled Teeth
XXX-XXXX 0757810	D6AM2	24	300mm	Milled Teeth

## Approvals

<b>Declarations</b>	REACH DoC
---------------------	-----------

## Similar Products

Stock No.	Brand	Product Name	Material Code	TPI	Working Length	Teeth Technology
XXX-XXXX 0757843	RS PRO	Hacksaw Blade	D6AM2	24	150mm	Milled Teeth
XXX-XXXX 0757844	RS PRO	Hacksaw Blade	D6AM2	18	300mm	Milled Teeth
XXX-XXXX 0757810	RS PRO	Hacksaw Blade	D6AM2	24	300mm	Milled Teeth

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories