

## 1 B 70

Combination spanner with same size each end

metric

Code **6004740** ETIM **EC002176**

EAN **4010886600474** UNSPSC **27-11-17-13**

Country of origin **Germany** eCl@ss **21-04-01-05**

Customs tariff number  
**82041100**



## Article description

- Acc. to DIN 3113, Form A, ISO 3318, ISO 7738
- Sizes 5 and 5.5 mm with hexagon ring, up from size 6 mm with UD profile
- Chrome-vanadium steel 31CrV3, chrome-plated
- Carefully forged and professionally machined
- Ring: 10° offset from shaft, with UD profile for gentle transmission of force
- Overloading indicated by deformation
- The offset ring ensures a better grip on deep-seated or inset nuts or bolts
- Top-grade industrial quality for the hardest of continuous use
- \* not standardised

## Article information

Contents [Qty of pieces]	<b>1</b>	Width of head 2 [mm]	<b>143 mm</b>
Net weight [kg]	<b>5,625 kg</b>	Head height 2 [mm]	<b>24 mm</b>
Total length [mm]	<b>755 mm</b>	Head height 1 [mm]	<b>35 mm</b>
Total width [mm]	<b>135 mm</b>	Width of head 1 [mm]	<b>105,0 mm</b>
Total height [mm]	<b>55 mm</b>	Mouth position 1	<b>15°</b>
Surface	<b>chrome-plated</b>	Height of offset 1	<b>53,5 mm</b>
Material	<b>Vanadium steel 31CrV3</b>	Ring profile	<b>bi-hex</b>
Standard	<b>not standardised</b>	Ring offset	<b>10°</b>
Width across flats 1 [mm]	<b>70</b>	Weight	<b>12,400 lbs</b>