

894 95

Single open ended spanner

metric

Code	ETIM
6578160	EC002130
EAN	UNSPSC
4010886657812	27-11-17-06
Country of origin	eCl@ss
Germany	21-04-01-01
Customs tariff number	
82041100	



Article description

- Acc. to DIN 894, ISO 3318
- Manganese phosphate finish up to 38 mm, steel-grey up from 41 mm
- Size 10 - 135 mm with angling hole
- Carefully forged and professionally machined:
- Jaw: ground precisely to exact nominal size for optimum contact areas
- Jaw set at 15°
- Secure grip thanks to profile shaft - very ergonomic and handy
- Overloading indicated by deformation
- * not standardised

Article information

Contents (Qty of pieces)	1
Net weight [kg]	6,335 kg
Total length [mm]	850 mm
Total width [mm]	192 mm
Total height [mm]	28 mm
Surface	steel-grey
Material	Vanadium steel 31CrV3

Standard	not standardised
Width across flats 1 [mm]	95
Head height 1 [mm]	25 mm
Width of head 1 [mm]	195,0 mm
Jaw set	15°
Ratchet function	no