

FEATURES

- **Sintered Bronze Material:** Provides excellent wear resistance and durability.
- **0.38 in Inside and Outside Diameter:** Ensures compatibility with a wide range of shafts and housings.
- **0.12 in Thickness:** Offers a compact solution for tight spaces.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads efficiently.
- **ISO 9001:2008, UKAS 001 Approved:** Meets international quality and safety standards.

RS PRO Sintered Bronze Thrust Washer, 0.38 in Diameter

RS Stock No: 528-209



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO sintered bronze thrust washer is designed to provide reliable support and reduce friction in axial load applications. Ideal for use in machinery where space is limited, it offers excellent performance under both dynamic and static loads.

General Specifications

Dynamic Load Rating	14 N/mm ²
Product Type	Thrust Washer
Static Load Rating	50 N/mm ²
Sub Type	Washer

Mechanical Specifications

Inside Diameter	0.38 in
Material	Sintered Bronze
Outside Diameter	0.38 in
Thickness	0.12 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

