

## Datasheet

### **RS Pro 0.4 mm Straight Conical Soldering Iron Tip for use with DS80 Digital Soldering Station**

RS Stock No: **665-4814**



## Product Details

RS Pro straight conical soldering iron tip is suitable for use with DS80 digital soldering station. It has a tip size of 0.4 mm. It provides a cost-effective, entry level soldering station for the intermittent / low volume user. The hand piece and tip is designed to enable rapid heat recovery required for Lead free soldering. It is complete with grounding stud/socket for critical applications and ESD work. It is supplied with UK converter plug. The operating temperature range is from 150 to 450 deg C.

## Features and Benefits

- DS80-T1 0.8 mm tip
- Pre- programmed to: 150°C, 300°C, 400°C
- Timer adjusted standby mode and auto power off (5 min steps)
- Soldering iron: 24 V/80W
- 3 programmable set point temperatures
- 230 V power supply



ENGLISH

### Specifications:

For Use With	DS80 Digital Soldering Station
Tip Shape	Straight Conical
Tip Size	0.4 mm