

12.5 (1/2") SQUARE DRIVE

12.5 1/2" 12.5 1/2"

RATCHETS 12.5 (1/2")





1993 U-20

REVERSIBLE RATCHET 1/2"

- ✔ Acc. to DIN 3122, ISO 3315
- ✔ Small, drop shaped head for confined areas
- ✔ Fine-toothed, with lever change and push-button release
- ✔ Non-slip 2-component handle with hanging hole
- ✔ For hand-operated sockets and accessories with square drive as per DIN 3120 - C 12.5, ISO 1174, ball locking device
- ✔ GEDORE vanadium steel 31CrV3, chrome-plated



12.5
1/2"



Code	No.	□"	■"	∠°	↳mm↵	↳	↳↵	↳	£
1436686	1993 U-20	1/2	12.5	6	270	37.5	536	5	

1993 U-20 SK

REVERSIBLE RATCHET 1/2"

- ✔ With 1/2" hexagon drive
- ✔ Torques specification required to standard DIN 3122 is exceeded
- ✔ Small, drop shaped head for confined areas
- ✔ Fine-toothed, with lever change
- ✔ Non-slip 2-component handle with hanging hole
- ✔ For hand-operated sockets with 1/2" hexagon no. 19 SK
- ✔ GEDORE vanadium steel 31CrV3, chrome-plated



12.5
1/2"



-45 %



Code	No.	□"	○"	∠°	↳mm↵	↳	↳↵	↳	£
2219492	1993 U-20 SK	1/2	12.5	6	270	21	510	1	



1993 U-10 L

REVERSIBLE RATCHET 1/2" long pattern

- ✔ Acc. to DIN 3122, ISO 3315
- ✔ With lever change
- ✔ Push-button release
- ✔ Non-slip 2-component handle with hanging hole
- ✔ Locks in the middle position: When the lever is flipped, it automatically engages for clockwise or counterclockwise operation
- ✔ For hand-operated sockets and accessories with square drive as per DIN 3120 - C 12.5, ISO 1174, ball locking device
- ✔ GEDORE vanadium steel 31CrV3, chrome-plated



12.5
1/2"




Code	No.	□"	■"	∠°	↳mm↵	↳	↳↵	↳	£
6154550	1993 U-10 L	12.5	1/2	11,25	350	41	696	5	

1993 U-10 T

REVERSIBLE RATCHET 1/2"

- Acc. to DIN 3122, ISO 3315
- With recessed lever change
- Push-button release
- Non-slip 2-component handle with hanging hole
- Locks in the middle position: When the lever is flipped, it automatically engages for clockwise or counterclockwise operation
- For hand-operated sockets and accessories with square drive as per DIN 3120 - C 12.5, ISO 1174, ball locking device
- GEDORE vanadium steel 31CrV3, chrome-plated

12,5
1/2"




Code	No.	□"	■	◊	↳mm↳	↳	↳	↳	£
6142620	1993 U-10 T	1/2	12.5	11,25	270	39	598	5	

1993 ALU-10

ALUMINIUM REVERSIBLE RATCHET 1/2"

- Design spec. similar to DIN 3122, ISO 3315
- Made from special-purpose drop-forged and hardened aluminium
- The mechanism as in all U-10 ratchets is made from high-quality steel
- With lever change
- Push-button release
- Non-slip 2-component handle with hanging hole
- Locks in the middle position: When the lever is flipped, it automatically engages for clockwise or counterclockwise operation
- For hand-operated sockets and accessories with square drive as per DIN 3120 - C 12.5, ISO 1174, ball locking device
- Extremely lightweight - just 340 g

12,5
1/2"




Code	No.	□"	■	◊	↳mm↳	↳	↳	↳	£
6142700	1993 ALU-10	1/2	12.5	11,25	270	39	340	5	

1993 U-3

REVERSIBLE RATCHET 1/2"

- Acc. to DIN 3122, ISO 3315
- With non-slip metal disc change, fine-toothed and robust
- Non-slip 2-component handle with hanging hole
- For hand-operated sockets and accessories with square drive as per DIN 3120 - C 12.5, ISO 1174, ball locking device
- GEDORE vanadium steel 31CrV3, chrome-plated

12,5
1/2"



Code	No.	□"	■	◊	↳mm↳	↳	↳	↳	£
6144240	1993 U-3	1/2	12.5	5	270	40.5	476	5	

VDE 1993 U




559



NC 1993 U-10



547



1940



212

