



# 10C / 40

- 40mm solid brass padlock body & 1800mm multi-strand octagonal steel cable
- Double locking
- Pin tumbler cylinder
- Hardened steel shackle
- Two keys provided
- 10mm cable diameter
- High tensile
- Protective durable coating
- Dual looped ends



| Body Width | Body Thickness | Shackle Diameter | Vertical Clearance | Horizontal Clearance | Approx. Height | Approx. Weight |
|------------|----------------|------------------|--------------------|----------------------|----------------|----------------|
| 40 mm      | 14 mm          | 6.35 mm          | 22 mm              | 21 mm                | 61 mm          | 0.12 kg        |