

## Features

- Alternative 12 /24 hour system
- Easily switch between Standard time and Summer time (DST)
- Up to 10 programmes of On & Off setting per day
- Time setting includes HOUR, MINUTE and DAY
- Manual override feature to set the timer switch to always on or off
- Random setting to have your lights to go on and off at random times during vacation

## RS PRO Plug-in Timer. 1.5" /2.3" LCD. 20 On/Off

RS Stock No.: 873-8851,873-8854,873-8857,873-8860



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

- Works with suitable pneumatic tools
- Used for Construction work areas, manufacturing facilities, automatic maintenance, home DIY etc.. • Open Type Hose Reel with hand Crank
- Heavy Duty Reinforced Steel Construction with Power Paint Coating
- ETHER Reinforced Polyurethane Hose:
- Great flexibility and user friendliness, even in sub-zero temperatures.
- Resistant to attacks from moisture and fungus.
- RoHS requirement and Silicon-free
- 360° Rotary Base for Easy Use
- 4pcs rubber stoppers to hold the reel in place when in use
- Includes mounting bracket and hardware for wall mounting
- Easy to mount and dismount from the wall for outdoor use
- Easily stored away

## General Specifications

Reinforced Polyurethane Hose	ETHER Base
Hose Colour	Blue
Temperature Range	-40°C to +60°C

## Mechanical Specifications

Article No	Hose ID	Hose Length	Lead Hose length	Working Pressure	Fitting Thread Size	Weight
873-8851	9.5 / 3/8	30M	110cm	15 / 200	3/8 + 3/8	8 kgs
873-8854	8 / 5/6	30M	110cm	15 / 200	1/4 + 1/4	6.5 kgs
873-8857	9.5 / 3/8	25M	110cm	15 / 200	3/8 + 3/8	7 kgs
873-8860	10 / 3/8	20M	110cm	15 / 200	3/8 + 3/8	6.5 kgs