
Item no.: 260-301
Product description: 2-CONDUCTOR TERMINAL BLOCK FOR SCREW OR
SIMILAR MOUNTING TYPES 3.2 MM Ø MOUNTING ADAPTER
AVAILABLE FOR TS 35 (209-123)



Produkt kann von Bild abweichen / product may differ

Packing unit 300 6*50 pieces

RoHS compliant

Product group	9 (Std Chassis Mt Blocks)
Cross section [mm ²]	0.08 - 1.5 mm ²
Cross section [AWG]	28 - 16 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	400 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	18 A
Weight	1.58 g
Color	gray
Wiring type	Side-entry
No. of connection Points	2
No. of potentials	1
Height	17 mm
Height	0.669 in
Width	5 mm
Width	0.197 in
Depth	25 mm

Depth	0.985 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
260-301	ABS	04-HG476174/1-PDA	400	17,5	1,5
260-301	BV	07436/C0	400	17,5	0,08-1,5
260-301	CCA	NL5800	400		1,5
260-301	CSA	18677-45	300	15	24-16
260-301	DNV	E-9215	400	18	1,5
260-301	GL	17295-00HH	400	17,5	1,5
260-301	KEMA	2110272.01	400		1,5
260-301	KR	HMB05880-EL002	400	17,5	1,5
260-301	LR	92/20242(E5)	400	17,5	1,5
260-301	PRS	TE/1718/880590/08	400		1,5
260-301	RMR	11130002	400	17,5	1,5
260-301	UR	E45172	300	10	28-16

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected