

# LONG LIFE CUTTING STONE

## PRO

- 1 High-quality silicon carbide for cutting various types of stone
- 2 Strong fibreglass net reinforces the disc



# PRO STONE BONDED CUTTING DISC

**PRO**


- ▶ For cutting stone efficiently
- ▶ Highly efficient for stoneworkers: Long Life
- ▶ Designed for cutting stone
- ▶ With 22.23 mm bore for standard locking nut angle grinders



| PRODUCT PROPERTIES    |             |                  |              |        |     |                | ORDERING INFORMATION |                        |                      |               |  |  |
|-----------------------|-------------|------------------|--------------|--------|-----|----------------|----------------------|------------------------|----------------------|---------------|--|--|
| Specification         | Diameter mm | Bore diameter mm | Thickness mm | X-LOCK | oSa | Packaging type | Pack quantity        | Minimum order quantity | Barcode 3 165 140... | Part number   |  |  |
| With depressed centre |             |                  |              |        |     |                |                      |                        |                      |               |  |  |
| C 30 S BF             | 115         | 22.23            | 2.5          | -      | -   | U0             | 1                    | 25                     | 658 324              | 2 608 603 173 |  |  |
| Straight              |             |                  |              |        |     |                |                      |                        |                      |               |  |  |
| C 30 S BF             | 115         | 22.23            | 3.0          | -      | -   | U0             | 1                    | 25                     | 658 362              | 2 608 603 177 |  |  |
| With depressed centre |             |                  |              |        |     |                |                      |                        |                      |               |  |  |
| C 30 S BF             | 125         | 22.23            | 2.5          | -      | -   | U0             | 1                    | 25                     | 658 331              | 2 608 603 174 |  |  |
| Straight              |             |                  |              |        |     |                |                      |                        |                      |               |  |  |
| C 30 S BF             | 125         | 22.23            | 3.0          | -      | -   | U0             | 1                    | 25                     | 658 621              | 2 608 603 178 |  |  |


**BOSCH**