

**ARCANOL-MULTITOP-5KG** [↗](#)

Bearing grease

Multi-purpose grease ARCANOL-MULTITOP

Technical information

Your current product variant

Grease category	MP	Multi-purpose greases
Package size	5 KG	5 kg bucket

Technical data

$\vartheta_{O \min}$	-50 °C	Operating temperature, min.
$\vartheta_{O \max}$	140 °C	Operating temperature, max.
ϑ_G	80 °C	Upper continuous limit temperature
$n \cdot d_M$	800.000 mm/min	Speed of rotation specific value
	Lithium soap	Thickener type
	Partially synthetic oil	Base oil type
v_{40}	82 mm ² /s	Base oil viscosity at +40°C
v_{100}	12,5 mm ² /s	Base oil viscosity at +100 °C
	2	NLGI class
	Multi-purpose grease	Grease category
ρ	0,87 kg/dm ³	Density
	5 kg bucket	Container
$\approx m$	5,4 kg	Weight