


ZB 5,LGS:FORTL.ZAHLEN 281-290 - Zack marker strip



1050017:0281  
<https://www.phoenixcontact.com/gb/products/1050017:0281>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, 10-section, horizontally labeled with the consecutive numbers: 281 ... 290, white, for terminal block width: 5.2 mm, mounting type: latching

Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1050017:0281  |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BG2122        |
| Product key                          | BG2122        |
| GTIN                                 | 4017918506988 |
| Weight per piece (including packing) | 1.266 g       |
| Weight per piece (excluding packing) | 1.066 g       |
| Customs tariff number                | 49119900      |
| Country of origin                    | DE            |

# ZB 5,LGS:FORTL.ZAHLEN 281-290 - Zack marker strip



1050017:0281

<https://www.phoenixcontact.com/gb/products/1050017:0281>

## Technical data

### Product properties

|              |                         |
|--------------|-------------------------|
| Product type | Labeled terminal marker |
| Pitch        | 5.2 mm                  |
| Type         | high                    |

### Marking

|          |             |
|----------|-------------|
| Printing | 281 ... 290 |
|----------|-------------|

### Mounting

|               |          |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

### Material specifications

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | white (RAL 9010)               |
| Material                               | PA                             |
| Flammability rating according to UL 94 | V2                             |
| Components                             | free from silicone and halogen |

### Environmental and real-life conditions

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
|---------------|--------------------------------|

#### Wipe resistance of inscriptions

|               |                                                |
|---------------|------------------------------------------------|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07            |
|               | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |

#### Ambient conditions

|                                                     |                   |
|-----------------------------------------------------|-------------------|
| Ambient temperature (operation)                     | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C             |
| Recommended humidity (storage/transport)            | 50 %              |

### Dimensions

|       |        |
|-------|--------|
| Width | 5 mm   |
| Pitch | 5.2 mm |

#### Text field

|                   |          |
|-------------------|----------|
| Text field width  | 5.15 mm  |
| Text field height | 10.50 mm |

### Standards and regulations

|                 |              |
|-----------------|--------------|
| Wipe resistance | DIN 30646    |
|                 | DIN VDE 0611 |

# ZB 5,LGS:FORTL.ZAHLEN 281-290 - Zack marker strip



1050017:0281  
<https://www.phoenixcontact.com/gb/products/1050017:0281>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000761 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)