

## 7MH5121-5AD00

SIWAREX WL230 LOAD CELL SB-S CA 10T C3 - NOMINAL LOAD 10 T - ACCURACY C3 - 6 M CABLE, 4 WIRE - MATERIAL NICKEL PLATED STEEL - TYPE OF PROTECTION IP67

List Price	Show prices
<b>Customer Price</b>	Show prices
Service & Support (Manuals, Certificates, FAQs...)	Download



Image similar

**Product**

Article Number (Market Facing Number)	7MH5121-5AD00
Product Description	SIWAREX WL230 LOAD CELL SB-S CA 10T C3 - NOMINAL LOAD 10 T - ACCURACY C3 - 6 M CABLE, 4 WIRE - MATERIAL NICKEL PLATED STEEL - TYPE OF PROTECTION IP67
Product family	Load cell
Product Lifecycle (PLM)	PM300:Active Product

**Price data**

Price Group	8W5
List Price	Show prices
Customer Price	Show prices
Surcharge for Raw Materials	None
Metal Factor	None

**Delivery information**

Export Control Regulations	AL : N / ECCN : N
Standard lead time ex-works	20 Day/Days
Net Weight (kg)	4,200 Kg
Package size unit of measure	Not available
Quantity Unit	1 Piece
Packaging Quantity	1

**Additional Product Information**

EAN	Not available
UPC	Not available
Commodity Code	84239010
LKZ_FDB/ CatalogID	WT01
Product Group	4913
Group Code	R3P5
Country of origin	China
Compliance with the substance restrictions according to RoHS directive	Since: 15.07.2015
Product class	A: Standard product which is a stock item could be returned within the returns guidelines/period.
WEEE (2012/19/EU) Take-Back Obligation	Yes
REACH Art. 33 Duty to inform according to the current list of candidates	

**Classifications**

	Version	Classification
eClass	6	27-32-03-02
eClass	7.1	27-32-03-02
eClass	8	27-32-03-02
eClass	9	27-32-03-02
eClass	9.1	27-32-03-02
ETIM	5	EC003997
ETIM	8	EC003997
UNSPSC	15	32-15-17-05