

FEATURES

- **Alloy Steel Construction:** Provides high strength and durability, ensuring long-lasting performance.
- **830 mm Overall Length:** Offers extended reach and leverage for various applications.
- **Claw End Design:** Enhances grip and functionality for effective prying and lifting.
- **ANSI-ESD S20.20:2021 Compliance:** Meets industry standards for safety and reliability.
- **REACH Compliant:** Ensures adherence to environmental and health regulations.

RS PRO Alloy Steel Pry Bar, 830 mm

RS Stock No: 555-902



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO Alloy Steel Pry Bar is a robust tool designed for heavy-duty applications where leverage and force are required. With a length of 830 mm, it is ideal for prying, lifting, and positioning tasks in industrial settings. The use of alloy steel ensures durability and resistance to wear, making it a reliable choice for professionals.

General Specifications

Claw Ended	Yes
Product Type	Pry Bar

Mechanical Specifications

Material	Alloy Steel
Overall Length	830 mm

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, REACH
---------------------	-----------------------------

