

PSZFON-0830 - PSZFON

General Part Information	
Product Description	PSZFON-0830
Article Number	33230
POPNut Type i	PSZFON
Standard Bulk Pack Quantity	2,000

Geometry / Dimensions	
Thread Size	M8
Body Type (open / closed) i	Open
Body Features i	Linear Knurls
Body Length (mm)	16.30
Min. Grip Thickness (mm)	0.50
Max. Grip Thickness (mm)	3.00
Head Style i	Flat Head
Hole Diameter (mm)	11.00
Head Diameter (mm)	14.80
Head Thickness (mm)	1.50
Barrel Diameter (mm)	10.90

Material / Weight	
Material i	Steel
Weight per thousand (kg)	5.7

