


FEATURES

- **DALI2, Push Dimming, PWM compatibility:** Offers versatile dimming options for enhanced lighting control
- **8.34 A driver current:** Ensures optimal power delivery to LED systems
- **Input voltage range of 100 – 277 V AC:** Supports a wide range of electrical systems
- **IP66 rating:** Provides protection against dust and water, suitable for outdoor use
- **Single output:** Simplifies installation and reduces wiring complexity
- **Constant Voltage operation:** Maintains stable output for consistent lighting performance

RS PRO 200W LED Driver, 24V Constant Voltage

RS Stock No: 642-785



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO LED Driver is designed to deliver reliable power for LED lighting systems. With a maximum output power of 200W and a constant voltage of 24V, it ensures consistent performance for demanding applications. Ideal for both commercial and industrial environments, this driver supports various dimming operations, providing flexibility and energy efficiency.

General Specifications

Dimming Operation	DALI2, Push Dimming, PWM
Number of Outputs	1
Operating Modes	Constant Voltage
Primary Type	AC
Product Type	LED Driver
Sub Type	Constant Voltage LED Driver

Electrical Specifications

Driver Current	8.34 A
Input Voltage	100-277 V ac
Input Voltage Type	AC
Maximum Output Power	200 W
Output Voltage	24 V

Protection Category

IP Rating	IP66
-----------	------

Approvals

Standards/Approvals	CE, EN55015, EN61000-3-2, EN61000-3-3, EN61000-4-2,3,4,5,6,11, EN61347-1, EN61347-2-13, EN61547, EN62493
---------------------	--